

smart H₂O for you, and your science



0 0 C

Thermo

RINSING LAB GLASSWARE SUPPLYING GENERAL LAB EQUIPMENT PREPARING AND DILUTING BUFFERS, REAGENTS, AND MEDIA

Thermo Scientific Barnstead Pacific TII water purification systems

Pure water production at 15°C, L/h	3, 7, 12, 20, or 40
Resistivity at 25°C, MΩ∙cm	10 - 15
Conductivity, µS/cm	0.1 - 0.067
TOC, ppb	<30
Removal, bacteria and particles, %	99

Multiple options for Type 2 water

- Converts tap water into high purity Type 2 water
- Up to 200 L/day of pure water for applications such as sample preparation or glassware rinsing
- Five permeate flow options of 3, 7, 12, 20, or 40 L/hr (UV lamp available for each flow option)
- Bench or wall mountable

Smart consumables

- The high performance reverse osmosis membrane is designed to remove approximately 98% of inorganic ions and 99% of all dissolved organic substances, as well as microorganisms and particles
- High purity water cartridge further purifies the reverse osmosis permeate to produce high purity water
- UV photo-oxidation at 254 nm controls microorganisms up to a 2-year lifetime (available on UV systems only)



15.00 MΩ•cm = resisitivity

20.3°C = water temperature

Easy-to-operate

- Temperature compensated resistivity/conductivity with accuracy of ±0.1°C
- Back-lit display, tiltable for easy viewing
- Reservoir fill-level indicated
- System parameters are code-protected, designed to prevent accidental changes to set points
- Water is dispensed directly from storage tank
- Optional printer for data recording and traceability
- Precise conductivity cell constant of 0.01 cm-1
- Microprocessor controlled continuous monitoring of all critical parameters

Pacific TII reservoirs

- Inert polyethylene reservoir stores high purity water safely
- Optional safety filters include a CO₂ adsorber to prevent conductivity increases from drawn-in CO₂. Sterile overflow prevents microorganisms from entering and contaminating reservoir water
- Wall mount optional for space-saving option (30 L and 60 L only)
- Recirculation of the water between the storage reservoir and Pacific TII system maintains water quality





Easy to operate with current status of system clearly indicated



Easy cartridge replacement



	Desifie TI	Pacific TII UV	Storage Reservoirs				
	Pacific TII Pacifi		30 L	60 L	100 L		
Product Dimensions H x W x D, mm (in.)	603 x 372 x 330 (24 x 15 x 13)		603 x 380 (24 x 15)	914 x 380 (36 x 15)	1249 x 380 (49 x 15)		
Product Weight kg (lbs.) w/o water	25 (51)		8 (18)	15 (33)	17 (38)		
Shipping Dimensions H x W x D, mm (in.)	800 x 600 x 600 (32 x 24 x 24)) mm (in)		706 x 455 x 430 (28 x 18 x 17)	940 x 410 x 495 (37 x 17 x 20)	1340 x 800 x 510 (53 x 32 x 20)
Shipping Weight kg (lbs.)	29 (64)		10 (22)	17 (38)	19.5 (43)		

Required Feed Water Quality					
Source	Tap water				
Free Chlorine	<0.1 mg/L				
Conductivity, µS/cm	<1,000				
SDI	<3				
pH Range	4 - 11				
Temperature, °C	2 - 35				
Pressure, psi (bar)	29 - 87 (2 - 6)				

Ordering information

Pacific TII System Options	Pacific TII 3	Pacific TII	Pacific TII 12	Pacific TII 20	Pacific TII 40			
All systems have a built-in wall bracket and include an RO membrane, a high purity water cartridge, and pressure regulator. UV lamp also included on applicable units.	System with UV	50132129	50132131	50132132	50131982	50132133		
	System without UV	50132121	50132123	50132124	50132125	50132127		
Required Accessories								
Pacific TII Reservoir Choose a reservoir that fits your needs.	See "Storage Reservoir Options"							
Double cartridge pretreatment system A 5 µm filter with activated carbon cartridge and a hardness stabilizer cartridge ship complete with two 10 inch filter housings with wall brackets. Used to control chlorine, organic impurities, particulates and control hardness for feed water with <250ppm TIS.			09.4000					
Optional Accessories								
Hand Dispenser Kit Hand dispenser with 3 meter tubing that connects to reservoir. Sl	50138221							
Printer Utilizes RS-232 interface for safe documentation of all	120V, 50/60Hz	AY1137X1						
measured values and faults with date and time in compliance with GLP-Guidelines.	230V, 50Hz	09.2207						
Replacement Consumables								
RO membrane Pacific TII 3, 7, 12 systems only require a single RO membrane Pacific TII 20 and 40 systems require two membranes as indic	22.0046	22.0046	22.0046	22.0046 (order 2)	22.0087 (order 2)			
High purity water cartridge	09.4011							
System UV lamp For UV systems only.	50139226							
Cleaning solution	CMX25							
Activated carbon cartridge with 5 μm prefilter	06.5201							
Hardness stabilizer cartridge	06.5452							
Storage Reservoir Options for Pacific TII systems	30L		60L		100L			
Storage reservoir	with level display	06.5033		06.5063	C	6.5083		
Choose a reservoir to meet your capacity needs. Water in reservoir should be used every 1-2 days.	with level display and recirculation/pressure pump	06.5032		06.5062	06.5082			
Required Accessories								
Sterile overflow for reservoir	06.5001							
CO_2 adsorber + sterile filter, 0.2 μ M	06.5002							
Optional Accessories								
UV lamp assembly for the reservoir, 230 V (not sold in U Ships complete with assembly and UV lamp.	06.5006							
Wall mounting bracket	06.5015 06.5016 n/		n/a					
Replacement Consumables								
UV lamp (for reservoir)			09.5002					

thermoscientific.com/purewater

© 2016 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

Australia +61 39757 4300 Austria +43 1 801 40 0 Belgium +32 53 73 42 41 China +800 810 5118 or +400 650 5118 France +33 2 2803 2180 Germany national toll free 0800 1 536 376 Germany international +49 6184 90 6000 India toll free 1800 22 8374 India +91 22 6716 2200 Italy +39 02 95059 552 Japan +81 3 5826 1616 Netherlands +31 76 579 55 55 New Zealand +64 9 980 6700 Nordic/Baltic/CIS countries +358 10 329 2200 Russia +7 812 703 42 15 Spain/Portugal +34 93 223 09 18 Switzerland +41 44 454 12 12 UK/Ireland +44 870 609 9203 USA/Canada +1 866 984 3766

Other Asian countries +852 2885 4613 **Countries not listed** +49 6184 90 6000



CE SP

BRWPPACIFICTII 0316